

TPX SCREWDRIVER TPX30 X 100MM L



- For use with tamper proof TX fastenings
- TT-MV PLUS steel alloy for greater strength and material flexibility
- Ergonomically designed bi-material handle for easy use with higher torque and faster speed
- Hole in the handle for hanging or for use as a T handle for extra torque or with a fall protection wire if needed
- The handle is moulded around the blade to ensure straightness and to allow larger blade wings which give a higher torque capacity

Screwdriver TPX30 x 100mm

General information

Country of origin: Taiwan
Barcode: 5020385062801
Tarriff code Europe: 8205400000
ECCN US: EAR99
ETIM: EC000801
UNSPSC: 27111701

Dimensions

Net weight (g): 99
Length: 216 mm

Attributes

Product type: Regular Screwdrivers
Material: TT-MV PLUS
Certificates: N/A
Size: TPX30
Shaft length (mm): 100
Shaft type: Round
Handle size: L
Tip: TPX
Tethering facility: Yes
Striking cap: No
T-drive facility: Yes

Features



 **DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 01-08-2024 19:48



Sandbergsvägen 3
441 39 Alingsås, Sweden