


# PXP4011/08P/5055 Datasheet

Product Name // Inline Cable Connector PXP4011 Series 8  
Contact Plug 5.0mm-5.5mm Cable

 [View Product Page](#)



## // Product Description:

- Inline Cable Connector
  - Sealed to IP66, IP68, IP69K when mated with compatible connector
  - Pin or Socket
  - 2, 3, 4, 6, 8, 10 or 12 Contact
  - Crimp or Solder Contacts available (supplied separately; use 13A/10A for 2, 3 Contact, 8A/5A for 4, 6, 8 Contact, 3A/3A for 10, 12 Contact)
- Contact insertion and crimp tools available (supplied separately)
  - Choice of cable acceptance 3mm-7mm depending on part code; supplied with Cable Gland and Collet colour coded by size, Cable Glands and Collets also available separately
  - PXP4082 Sealing Cap available separately to maintain IP rating of unmated connectors
  - Mate with Flex Connector PXP4010

## // General Information:

|                                 |                                                   |
|---------------------------------|---------------------------------------------------|
| Product Display Title:          | Inline Cable Connector                            |
| Product Family:                 | Circular Power Connectors                         |
| Product Series:                 | 4000 Series Buccaneer                             |
| Approvals:                      | UL                                                |
| Body Material:                  | Polycarbonate/Polybutylene Terephthalate (PC/PBT) |
| Body Material Type:             | Plastic Body                                      |
| Contact Type:                   | Plug Contact                                      |
| Coupling Type:                  | Screw                                             |
| Current Max:                    | 8A                                                |
| Diameter Over Coupling Ring Mm: | 19.7mm                                            |
| Flamability Rating:             | UL94V-0                                           |
| Function:                       | Inline Cable Connector                            |
| Ip Rating:                      | IP66                                              |
| Max Cable Entry Size:           | 5.5mm                                             |
| Min Cable Entry Size:           | 5.0mm                                             |
| Max Contact Accomodation Awg:   | 20AWG                                             |
| Min Contact Accomodation Awg:   | 18AWG                                             |
| Max Contact Accomodation Mm2:   | 0.75mm2                                           |
| Min Contact Accomodation Mm2:   | 0.5mm2                                            |
| Max Operating Temperature:      | +120°C                                            |
| Min Operating Temperature:      | -40°C                                             |
| Number Of Contacts:             | 8 Contacts                                        |
| Voltage Max:                    | 320V                                              |

### // Product PDF Links

-  [4000 Series power connectors...](#)
-  [4000 Series power connectors...](#)

### // Product 3D CAD Model Links

-  [PXP4011/08P/50553D CAD Model](#)

### // Product Certificate Links

-  [UL & CSA EN214792 - 4000 Series...](#)
-  [VDE Certificate - 4000 Series...](#)
-  [IP68 Test Certificate - 4000...](#)
-  [IP69X Test Certificate - 4000...](#)
-  [Salt Spray Test Certificate - 4000...](#)



Have a question or project enquiry  
you'd like to talk to us about?



[Click Here To Contact Us](#)