

A660 - CS Cut E18 PU Glove

Collection: Cut Resistant

Range: Hand Protection

Materials: HPPE, Nylon, Steel Fibre, Elastic, Elastane

Dipping:

Inner Pack: 12

Outer Carton: 144

Product information

18 gauge cut level E cut resistant glove with PU coating offering secure grip in dry and light oily handling environments. A reinforced thumb crotch adds extra durability. The breathable 18 gauge liner offers outstanding dexterity and comfort. Suitable for use with touchscreen devices. Reflective label increases glove visibility in low light conditions.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (3X42E)

ANSI/ISEA 105: 2016 CUT Level (A5)

ANSI/ISEA 105: 2016 ABRASION Level (4)

ANSI/ISEA 105: 2016 PUNCTURE Level (3)



Features

- Level E cut resistance
- 18 gauge liner provides excellent comfort, freedom of movement and superb tactile ability
- Smooth PU coating for increased abrasion resistance
- Reinforced thumb crotch for extra protection and durability
- This glove can be used with most mobile touchscreen devices
- Reflective label for improved visibility
- Palm dipped to increase dexterity and ventilation
- CE certified
- Retail tag which aids presentation for retail sales
- UKCA marked
- OEKO-TEX® STANDARD 100 approved



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A660 - CS Cut E18 PU Glove Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/20012-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
SATRA Technology Park
NN16 8SD, United Kingdom
Cert No: AB0321/20355-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A660K8RXS	Black	50.0	30.0	37.0	0.0400	0.0555	5036108360888	25036108849660
A660K8RS	Black	50.0	30.0	37.0	0.0440	0.0555	5036108360864	25036108849646
A660K8RM	Black	50.0	30.0	37.0	0.0490	0.0555	5036108360857	25036108849639
A660K8RL	Black	50.0	30.0	37.0	0.0600	0.0555	5036108360840	25036108849622
A660K8RXL	Black	50.0	30.0	37.0	0.0550	0.0555	5036108360871	25036108849653
A660K8RXXL	Black	50.0	30.0	37.0	0.0590	0.0555	5036108360895	25036108849677