

RAFIX insulated housing 22 mm, 3 mounting positions, light gray



fields of application

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Industrial robots

description

technical data

➤ general

Installation points	3 pcs.
Color	light gray
Packaging unit	1 pcs.
net weight	240 g
Degree of protection, front side, according to DIN EN 60529	IP65
Degree of protection, rear side, according to DIN EN 60529	IP65
MOQ order	5 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

- [RAFI eCatalog](#)

➤ mounting diameters

Outside dimension, length	100 mm
Outside dimension, width	115 mm
Outside dimension, height	74 mm
Mounting hole	22.3 mm

drawings**Dimensioned drawing**