

LED Sensor-Switched Security Light SSL 40 A with infrared motion detector 50 lm+40 lm



Product number 1173240020
EAN 4007123674381

DESCRIPTION

- Automatic switch-on in the event of a power failure, removal from the charging station or movement in the dark.
- The front light of the security light switches to night light mode in the dark and automatically increases the brightness as soon as movement is detected.
- Super-bright SMD LEDs with up to 3 hours of illumination when the battery is fully charged.
- Infrared motion detector with 90° horizontal detection angle and max. 3 m range.
- Can be used outside the charging cradle as a torch with 1 SMD LED or as an area light with 9 SMD LEDs.
- Built-in Li-Ion battery is charged inductively.
- Charging cradle 230 V, 50 Hz.

TECHNICAL DATA

Luminous flux	50 lm	Light duration max.	3.5 h
Total luminous flux secondary source	40 lm	Battery charging time approx.	15 h
Power consumption	1.2 W	Number of batteries	1
Colour temperature	3000 K	Battery type	Built-in battery pack
Colour rendering index	80-89 (class 1B)	Battery technology	Lithium-ion
Nominal input voltage	230 V	With socket outlet	No
Lifetime	35000 h	Protection class	II
Battery capacity	0.5 Ah	Degree of protection (IP)	IP20
Battery voltage	3.7 V	Colour	white

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.19 kg
Weight of product (without packaging)	0.14 kg	Dimension LxWxH (incl. packing)	6.5 cm x 9 cm x 15.3 cm
Dimension LxWxH (without packing)	6 cm x 8 cm x 11 cm		