

PRODUCT-DETAILS

# TY27M-3

## CABLE TIE 120LB 13IN ORANGE NYLON



### General Information

Extended Product Type	TY27M-3
Product ID	7TAG009370R0024
EAN	5414363063285
Catalog Description	CABLE TIE 120LB 13IN ORANGE NYLON
Long Description	High Performance Cable Tie, Orange Color Nylon 6.6, Length of 343mm (13.5 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -20 Degrees Celsius (-4 F) to 85 Degrees Celsius (185 F)

### Ordering

EAN	5414363063285
UPC	786210845012

### Container Information

Package Level 1 Units	500 piece
Package Level 1 Width	14 in 356 mm
Package Level 1 Depth / Length	22 in 559 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	14 in 356 mm
Package Level 2 Height	9.5 in

	241 mm
Package Level 2 Depth / Length	22 in 559 mm

### Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

### Additional Information

Effective Date	19670831
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY27M-3
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY27M-3

### Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

