



3
 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN Future HS 1000 FR

The Future HS1000FR worklight is a new development from the torch specialist ANSMANN:

- Two brightness levels, 100% and a 20% energy saving mode
- Operating time approx. 6 hours at 100% or 32 hours at 20% hours
- 5W digital white LED, producing 330 lumens at 100% and 70 lumens at 20%
- Beam length of up to 650m at 100% and 300m at 20%
- Highly efficient focusable reflector system with simple, smooth focussing
- Powered by a 3.7V 4400mAh, non-removable, lithium Ion rechargeable battery pack
- Included is a USB powered wall mountable charging station and will charge the battery in approx. 13 hours
- Mains failure electronics make this torch easy to locate in the dark, ideal for combating unexpected power cuts
- A clear LED indicator above the power switch lights when the torch is switched on, and also indicates status whilst charging (orange = charging, green = charged).

INFORMATION

Product name: Future HS1000FR
Article number: 1600-0055-UK
EAN-Code: 4013674026562
Product: 656g
Packing + Product: 838g

Packing unit: 6
Customs tariff number: 85131000