

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637
<https://www.phoenixcontact.com/gb/products/0826637>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, yellow: without print, mounting type: slide-on, cable diameter: > 16 mm, text field height: 2.6 mm, text field width: 4.3 mm

Your advantages

- The printed individual markers are pushed onto the corresponding holders
- Cable markers for marking cables and conductors with larger cross sections

Commercial data

Item number	0826637
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG2312
Product key	BG2312
Catalog page	Page 245 (C-3-2019)
GTIN	4046356414494
Weight per piece (including packing)	0.157 g
Weight per piece (excluding packing)	0.143 g
Customs tariff number	39269097
Country of origin	SE

Technical data

Product properties

Product type	Labeled conductor marker
Type	Marking strip/label

Marking

Printing	without print
----------	---------------

Mounting

Mounting type	slide-on
---------------	----------

Material specifications

Color	yellow (RAL 1018)
Material	PVC
Flammability rating according to UL 94	V2
Components	Free from silicone and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/gb/products/0826637>

Test duration	96 h
---------------	------

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Dimensions

Width	4.3 mm
Length	11.3 mm

External dimensions

Outside diameter	> 10 mm ... 136 mm
------------------	--------------------

Text field

Text field width	4.3 mm
Text field height	2.6 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Please specify the required marking with order: Minimum order per imprint: 1 packing unit
---------	---

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/gb/products/0826637>

Classifications

ECLASS

ECLASS-13.0	27281102
-------------	----------

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/gb/products/0826637>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk