



### Main

Product range	Mureva BOX
Product type	Junction box
Colour	Grey RAL 7035
Quantity per package	1 piece

### Complementary

Mounting	Surface
Cable entry	Grommets
Fixing mode	Screw-fixed cover
Interior dimensions	175 x 150 x 80 mm
Number of cable entries	2 grommets Ø 32 mm 10 grommets Ø 25 mm
Material	SBS (styrene butadiene styrene) grommet PP (polypropylene) cover
Electrical insulation class	Class II according to IEC 536
Height	90 mm
Width	195 mm
Depth	165 mm
Product weight	0.4 kg

### Environment

Operating temperature	-25...40 °C
IK-Class	IP55 according to IEC 60529
IK-Class	IK07 according to EN 50102
Glow wire temperature	750 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 1026 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Period	18 months
--------	-----------