

## Features

- Lightweight and flexible
- Length 25m
- ISO 3821:2010

## RS PRO Hose Pipe

RS Stock No.: 146-7760, 146-7761



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

Black, flexible hose for argon and nitrogen. Mainly for use in industrial argon-welding applications.

Specially developed to prevent moisture from permeating into the hose from the outside. A very strong, non-porous weld is thus achieved.

**General Specification**

Brand	RS PRO
Features	Flexible
Materials	EPDM, SBR
Colour	Black
Length	25m
Suitable Applications	Gas
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-25°C
Hose Pipe Action	Transfer
Standards Met	EN ISO 3821:2010

**Products in series**

Stock No.	Lenght	Inner Diameter	Outer Diameter	Colour
146-7760	25m	5mm	11mm	Black
146-7761	25m	6,3mm	13,3mm	Black