

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [120341-0150](#)
Status: **Active**
Overview: [industrial ethernet solutions](#)
Description: Micro-Change® M12 CAT6A Back Panel-Mount Receptacle, 8 Poles, Female (Straight), 0.0185m (.728") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	120341
IP Rating	IP67
Overview	industrial ethernet solutions
Performance Category	6A
Product Name	Micro-Change® (M12) Cat6A
Type	PCB Mount
UPC	884982937666

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	X-coded
Length	0.0185m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M12 x 1.0
Net Weight	19.500/g
Orientation	Straight
Panel Mount	Back
Poles	8
Temperature Range - Operating	-40°C to +70°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	.5A
Voltage - Maximum	48V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-120341-150
---------------	---------------



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Pb

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[120341Series](#)

Mates With

[120341 Micro-Change® CAT6A Cable Assemblies](#)