

Eaton DEO200

Catalog Number: DEO200

Fuse-link, LV, 200 A, AC 415 V, BS88, 31 x 110 mm, gL/gG, BS

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage British standard fuse	DEO200
	UPC 051712839648
EAN 5027590497794	Product Length/Depth 110 mm
Product Height 29.5 mm	Product Width 31 mm
Product Weight 145 g	Warranty Not Applicable
Compliances RoHS Compliant	



Electrical rating

Amperage Rating

200 A

Breaking capacity

80 kA

Interrupt rating

80 kAIC

Rated switching capacity

80 kA

Voltage rating

415 V

Voltage type

AC

Physical details

Color

None

Fuse type

DEO

General information

Class

Class gG/gL

Connection

94 mm fixing centre

Construction size

Other

Fitted with:

Offset bolted tags

Fuse indicator

None

Fuse shape

Offset bolted tags

Insulated metal gripping lugs (IMGL)

No

Utilization category

gL/gG (cable protection/equipment protection)

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Compliance information

[UKCA DEO OSD motor start](#)

[CE DEO OSD motor start](#)

Specifications and datasheets

[Eaton Specification Sheet - DEO200](#)

Technical data sheets

[4117 DEO fuses](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)