

**Supplier:** ROLINE  
**Article Number:** 21.15.1381-40



...



## Description

Patch cable for networking connections between devices. Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded copper wire. Complete braid shielding. Pairs shielded with aluminium clad polyester foil.

For a structured cabling system we recommend to use the following components: ROLINE Cat.6 S/FTP Cable, Solid Wire, AWG23: 21.15.0890 (100 m), 21.15.0891 (300 m); ROLINE Cat.6 Flush Mount Wall Jack, shielded: 25.16.8492 (white), 25.16.8493 (ivory); ROLINE Cat.6 Surface Mount Wall Jack, shielded: 25.16.8392 (white), 25.16.8393 (ivory); ROLINE Cat.6 19" Patch Panel, 24 Ports, shielded: 26.11.0351 (light grey), 26.11.0361 (black); ROLINE Cat.6 S/FTP Patch Cord, grey, 5 m: 21.15.0835. The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2365b-10-E (with flush mount)/z2364b-10-E (with surface mount).

## Technical Data - Overview

---

<b>Product group</b>	Twisted Pair Cable
<b>Conveyance good</b>	No
<b>Shield type</b>	SFTP
<b>Transfer quality</b>	Cat. 6 / Class E
<b>Impedance</b>	10 0 Ohm
<b>Quantity of wires</b>	8
<b>Conductor type</b>	Wire
<b>Crossed</b>	No
<b>Halogen free cable</b>	No
<b>Connector Type RJ45</b>	Standard

We reserve the right to amend any or all information without prior notice. Furthermore, all prices and offers are subject to change. We assume no responsibility for misprints or the accuracy of technical information. Product pictures and/or graphics are of an exemplary nature and can deviate from the original.