

Main

Range	Odace
Product or component type	Cover plate
Product destination	Socket-outlet
Type of packing	Plastic bag
Quantity per set	Set of 10

Complementary

Outlet poles configuration	2P + E
Outlet standard deviation	French
Fixing mode	Clip-in
Colour tint	White (RAL 9003)
Surface finish	Glossy
Surface treatment	Antibacterial
Material	Thermoplastic ABS-UV stabilised
Height	71 mm
Width	71 mm
Depth	8.2 mm
Material	Thermoplastic ABS-UV stabilised
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
IP degree of protection	IP20

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
IK degree of protection	IK04

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes