



---

**PRODUCT-DETAILS**

# **AT16/M16/C90/BLY**

## **90D PA66 FITTING M16 16MM-BLY**



---

**General Information**

Extended Product Type	AT16/M16/C90/BLY
Product ID	7TCA296170R0112
EAN	5020963037962
Catalog Description	90D PA66 FITTING M16 16MM-BLY
Long Description	Adaptalok ATS, 90 Degree Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 16mm, M16 Thread, Polyamide (Nylon) 66/TPE, Black with Yellow Elastomer

---

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

---

**Ordering**

EAN	5020963037962
UPC	786210257013

---

**Technical**

Number of Batteries	0
Color	Black/Yellow Elastomer
Material	Polyamide/Nylon 6.6
Size	NC 16mm

**Environmental**

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

**Container Information**

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963037962
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

**Certificates and Declarations**

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

**External Classifications and Standards**

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

**Categories**

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

