

## Cat5e Patch Cable with Snagless RJ45 Connectors - 2m, White

Product ID: 45PAT2MWH



The 45PAT2MWH Cat5e patch cable (2m) meets or exceeds all Cat 5e cable specifications to ensure reliable Ethernet network connections, and features a durable white PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles, reducing the risk of cable failure.

Constructed of only top quality materials, this Cat5e patch cord delivers reliable performance and is backed by our lifetime warranty.

### **100% copper for outstanding value**

Get the highest value for your cable investment with our Cat 5e cables, each one manufactured using high-quality copper conductors.

## **24-gauge wire for high-performance network connection**

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

## **50-micron gold connectors provide peak conductivity**

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

### Certifications, Reports and Compatibility



### Applications

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

### Features

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Type	Snagless
	Fire Rating	CM Rated
	Number of Conductors	4 pair UTP
<b>Performance</b>	Cable Rating	CAT5e - 350 MHz
<b>Connector(s)</b>	Connector A	1 - RJ-45 Male
	Connector B	1 - RJ-45 Male
<b>Physical Characteristics</b>	Cable Length	2 m [6.6 ft]
	Color	White
	Conductor Type	Stranded Copper
	Product Height	0.000
	Product Length	2 m [6.6 ft]
	Product Width	0.000
	Weight of Product	75 g [2.6 oz]
	Wire Gauge	24 AWG
<b>Packaging Information</b>	Package Height	23 mm [0.9 in]
	Package Length	22 cm [8.7 in]
	Package Quantity	1
	Package Width	20 cm [7.9 in]
	Shipping (Package) Weight	84 g [3 oz]
<b>What's in the Box</b>	Included in Package	1 - 2m White Snagless Cat5e UTP Patch Cable

Product appearance and specifications are subject to change without notice.