

Features

- LED Spacer Support
- Reliable and rugged
- RoHS Compliant

RS PRO LED HOLDER

RS Stock No.: 0227837



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Standard T-1 0227837 led Spacer support. Reliable and rugged. The product itself will remain within RoHS compliant Version.

General Specifications

LED Colour	Water clear
Dimensions	7x11 , NYLON66/PC (UL)

Mechanical Specifications

Mechanical Life

Recommended Soldering Pad Dimensions
Soldering Temperature : 260°C for 5 Seconds

A mechanical drawing of a component, likely a soldering pad, showing dimensions in millimeters and inches. The drawing includes a top view and a side view. The top view shows a rectangular shape with a central circular feature. The dimensions are: 9.3 [0.366] mm for the total width, 7 [0.276] mm for the width of the central feature, and 1.7 [0.067] mm for the width of the side flange. The side view shows a height of 7.2 [0.283] mm for the total height, 5.1 [0.201] mm for the height of the central feature, and 7 [0.276] mm for the height of the side flange.

Article	Material	Colour
0227837	Nylon66/PC (UL)	Water Clear

Notes:

All dimensions are in millimeters (inches).
Tolerance is ± 0.25 mm (.010") unless otherwise noted.
Lead spacing is measured where the leads emerge from the package.
Specifications are subject to change without notice.