

LONG LIFE DRILLING REINFORCED CONCRETE

EXPERT SDS max-8X Hammer Drill Bits

EXPERT

- ① Exceptionally durable drill bit tip with Bosch Carbide Technology
- ② Punch through reinforced concrete with a 4-cutter full carbide head
- ③ Highly resistant drill tip connection thanks to Bosch's special welding process



* vs. Bosch SDS max-4



BOSCH

EXPERT SDS MAX-8X HAMMER DRILL BIT



- ▶ Ideal for drilling holes in reinforced concrete, e.g. for chemical anchor setting and/or rebar connections
- ▶ Best for construction workers: long lasting and powerful
- ▶ Lasts up to 3x longer than Bosch SDS max-4 Drill Bit
- ▶ Fits all SDS max rotary hammer drills



PRODUCT PROPERTIES			ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
Pack of 1							
12.00	200	340	P1h	1	1	532 752	2 608 900 201
12.00	400	540	P1h	1	1	532 769	2 608 900 202
12.00	600	740	P1h	1	1	532 776	2 608 900 203
12.00	800	940	P1h	1	1	532 783	2 608 900 204
14.00	200	340	P1h	1	1	532 813	2 608 900 207
14.00	400	540	P1h	1	1	532 820	2 608 900 208
14.00	600	740	P1h	1	1	532 837	2 608 900 209
14.00	800	940	P1h	1	1	532 844	2 608 900 210
16.00	200	340	P1h	1	1	532 882	2 608 900 214
16.00	400	540	P1h	1	1	532 899	2 608 900 215
16.00	600	740	P1h	1	1	532 905	2 608 900 216
16.00	800	940	P1h	1	1	532 912	2 608 900 217
18.00	200	340	P1h	1	1	532 950	2 608 900 221
18.00	400	540	P1h	1	1	532 967	2 608 900 222
18.00	600	740	P1h	1	1	532 974	2 608 900 223
18.00	800	940	P1h	1	1	532 981	2 608 900 224
20.00	200	320	P1h	1	1	533 025	2 608 900 228
20.00	400	520	P1h	1	1	533 032	2 608 900 229
20.00	600	720	P1h	1	1	533 049	2 608 900 230
20.00	800	920	P1h	1	1	533 056	2 608 900 231
22.00	200	320	P1h	1	1	533 070	2 608 900 233
22.00	400	520	P1h	1	1	533 087	2 608 900 234
22.00	600	720	P1h	1	1	533 094	2 608 900 235
22.00	800	920	P1h	1	1	533 100	2 608 900 236
24.00	200	320	P1h	1	1	533 124	2 608 900 238
24.00	400	520	P1h	1	1	533 131	2 608 900 239
25.00	200	320	P1h	1	1	533 148	2 608 900 240
25.00	400	520	P1h	1	1	533 155	2 608 900 241
25.00	600	720	P1h	1	1	533 162	2 608 900 242
25.00	800	920	P1h	1	1	533 179	2 608 900 243
26.00	200	320	P1h	1	1	533 193	2 608 900 245
26.00	400	520	P1h	1	1	533 209	2 608 900 246
28.00	200	320	P1h	1	1	533 216	2 608 900 247
28.00	400	520	P1h	1	1	533 223	2 608 900 248
28.00	600	720	P1h	1	1	533 230	2 608 900 249
28.00	800	920	P1h	1	1	533 247	2 608 900 250
30.00	200	320	P1h	1	1	533 261	2 608 900 252
30.00	400	520	P1h	1	1	533 278	2 608 900 253



BOSCH

EXPERT SDS MAX-8X HAMMER DRILL BIT

PRODUCT PROPERTIES			ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
32.00	200	320	P1h	1	1	533 285	2 608 900 254
32.00	400	520	P1h	1	1	533 292	2 608 900 255
32.00	600	720	P1h	1	1	533 308	2 608 900 256
32.00	800	920	P1h	1	1	533 315	2 608 900 257
Pack of 5							
12.00	200	340	P0h	5	1	533 346	2 608 900 260
16.00	200	340	P0h	5	1	533 353	2 608 900 261
16.00	400	540	P0h	5	1	533 360	2 608 900 262
18.00	200	340	P0h	5	1	533 377	2 608 900 263
18.00	400	540	P0h	5	1	533 384	2 608 900 264
20.00	200	320	P0h	5	1	533 391	2 608 900 265
20.00	400	520	P0h	5	1	533 407	2 608 900 266
22.00	400	520	P0h	5	1	533 414	2 608 900 267
24.00	400	520	P0h	5	1	533 421	2 608 900 268
25.00	400	520	P0h	5	1	533 438	2 608 900 269
32.00	400	520	P0h	5	1	533 445	2 608 900 270



BOSCH