



D26500K

4 mm Electric Planer

Features and Benefits

- A powerful planer that copes effortlessly with hard woods, even at maximum depth of cut, giving a smooth, consistent finish
- Left and right chip ejection for convenience
- Front handle depth control in clearly marked 0.1 mm steps for accurate setting with positive indexing
- Rubber coated front and main handles eliminates slipping for greater comfort and control
- A large planer blade drum rotating at high speed provides an excellent finish
- 3 chamfering grooves in the front shoe simplify precision fitting jobs

Standard Equipment

- Tungsten carbide tipped reversible blades
- Depth Guide
- Heavy duty carrying case
- Dust extraction spout
- Chip ejector
- Chip deflector

Specifications	
Power Input	1050 Watts
Power Output	620 Watt
No Load Speed	13500 rpm
Maximum Depth of Cut	4 mm
Planer Width	82 mm
Rebating Depth	25 mm
Shoe Length	320 mm
Drum Diameter	64 mm