



ENGLISH

Datasheet

# RS Pro Pro 20W LED 110V Task Light

RS Stock No: 176-8532



This RS Pro 20W LED 110V Task Light is ideal for all site lighting requirements. It incorporates a built in floor stand and is made from strong yellow nylon body with polycarbonate clear diffuser and mirror reflector.

It comes fitted with super bright LED's, a 3m lead and 16A plug



ENGLISH

### Typical Properties

Material	Nylon and Polycarbonate
Wattage	20W
Lumens	2000Lm
Lumen Efficiency	100 Lm/W
Beam Angle	120°
Voltage	110V / 50Hz
Lamp Type	Fixed Sanan LED
CCT	6400K
Colour Temp	Daylight
IP Rating	IP44
Operating Temp	-20°C to 50°C