

## Features

- Polished Stainless Steel Scraper Blade
- Soft Grip Handles with Hanging Holes
- Suitable for a Wide Variety of Application
- 32mm Straight type Scraper
- Hammer Cap – Permits Careful Use with Hammer

## RS PRO Stainless Steel Scraper, 32mm Straight

RS Stock No.: 0246384



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

### RS PRO Stainless Steel Scraper, 32mm Straight

RS PRO angle scraper is made by stainless steel blades which thickness of 1.0 mm. It has reinforced strike zone.

- 215mm (Length), 1.1mm (Thickness)
- Blade Material: Stainless Steel
- Handle – PP/TPR Grip with Metal Hammer End
- Size: 32mm (W) Straight Type Blade

## General Specifications

Type	Scraper
Material	Blade- Stainless Steel Handle – PP/TPR Grip with Metal Hammer End
Number of Pieces	1
Non Sparking	No

## Mechanical Specifications

Hammer Cap	Zinc Alloy
Finish -Blade	Polished
Length	220mm
Blade Width	32mm (Straight)

## Similar Products

Stock No.	Brand	Product Name	Blade Size	Blade Thickness	Handle
0246383	RS PRO	Scraper set, 3pcs	32mm, 32mm, 50mm	1.0mm	PP/TPR Grip with Metal End
0246384	RS PRO	Scraper Straight	32mm,	1.0mm	PP/TPR Grip with Metal End
0246386	RS PRO	Scraper Angle	32mm,	1.0mm	PP/TPR Grip with Metal End
0246387	RS PRO	Scraper Straight	50mm	1.18mm	PP/TPR Grip with Metal End
0246389	RS PRO	Scraper 5 in 1	75mm	1.12mm	PP/TPR Grip with Metal End