

306 50

Ring slogging spanner

Code	ETIM
6475860	EC002188
EAN	UNSPSC
4010886647585	27-11-17-05
Country of origin	eCl@ss
Germany	21-04-01-03
Customs tariff number	
82041100	



Article description

- Top-grade industrial quality for the hardest of continuous use
- For heavy-duty work
- Special sizes available on request up to 250 mm
- Up to length 435 mm made of chrome vanadium steel 31CrV3, from length 480 mm made of material C35
- * not standardised
- Acc. to DIN 7444

Article information

Contents (Qty of pieces)	1	Standard	DIN 7444
Net weight [kg]	1,093 kg	Width across flats l [mm]	50
Total length [mm]	250 mm	Head height l [mm]	23,5 mm
Surface	oiled	Width of head l [mm]	80,0 mm
Material	31CrV3	Ring profile	UNIT-DRIVE