



### Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D40A...D80A 4P LC1DT60A...DT80A

### Complementary

Mounting location	Front
Mounting mode	By clips
Suppressor technology	Varistor (peak limiting)
[Uc] control circuit voltage	50...127 V DC 50...127 V AC 50/60 Hz
Maximum peak voltage	2 Uc
Net weight	0.02 kg

### Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------