

Eaton 138364

Catalog Number: 138364

Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure. Profile terminal 51x28 mm

General specifications



Product Name	Catalog Number
Eaton xEffect SASY 60i busbar terminal	138364
EAN	Product Length/Depth
4015081351442	103 mm
Product Height	Product Width
45 mm	82 mm
Product Weight	Compliances
0.705 kg	RoHS conform

Product specifications

Used with

Double T profile
185 mm system
60 mm system
Connection

Special features

Termination to busbars
without drilling
Put a spacer between the
laminated copper busbars
when connecting in parallel

Type

185 mm system
60 mm system
Connection

Width clamp

82 mm

Busbar thickness - max

40 mm

Busbar thickness - min

40 mm

Busbar width - max

30 mm

Busbar width - min

30 mm

Conductor cross section - max

750 mm²

Rated operational current (I_e) - max

1600 A

Functions

Profile terminal
Connections

Rated operation current (I_e)

1600 A

Suitable for

Strip conductor connection
T-rail

Resources

Brochures

[eaton-xeffect-sasy60i-customer-success-story-css-wagner-mueller-en-us.pdf](#)

Catalogs

Product Range Catalog Switching and protecting motors
[eaton-xeffect-sasy-60i-fk4300-1167gb-en-us.pdf](#)

Certification reports

[eaton-xeffect-sasy-60i-declaration-of-conformity.pdf](#)

Drawings

[eaton-control-panels-xeffect-sasy-profile-terminal-dimensions-002.eps](#)
[eaton-control-panels-xeffect-sasy-profile-terminal-3d-drawing.eps](#)

Installation instructions

[IL123005ZU](#)

Rated operational current

1600 A

Terminal capacity (conductor)

5 mm - 28 mm (51x)

750 mm² (Cu band)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia