

Datasheet

## RS Pro Right Angle 50Ω Cable Mount BNC Connector Plug, Crimp Termination RG174

RS Stock No: **546-3894**



### Product Details

RS Pro right angle cable mount BNC connector plug features a crimp ferrule, nickel plated body, gold plated centre contact and is for use with a variety of RF coaxial cable types. This male connector plug has 50 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C. This connector plug is suitable for a variety of applications including video signalling and test equipment.

### Features and Benefits

- Brass construction with nickel and gold plated contacts
- Crimp termination method
- Male connector
- RS BNC connectors are suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Body Orientation	Right Angle
Body Plating	Nickel
Cable Type	RG174
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 $\Omega$
Mounting Type	Cable Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Crimp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-20 to +80°C
Standards Met	RoHS Compliant
Voltage Rating	500 V Maximum