### LED88PIRN

# 6.5W LED Energy Saver PIR Bulkhead Light

#### **Features & Benefits**

- Powerful 6.5W LED energy saving bulkhead light.
- · Ideal for both indoor and outdoor installation.
- Colour temperature: 3700K to 4200K.
- Dusk until Dawn mode
- Simple and quick to fit with fast-fix terminal block connection



#### **Technical Data**

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class II
Operating Temperature	-20°C to +40°C
Ingress Protection Rating	IP55
Setting Type	Dial
Max Mounting Height (Mtr)	1.8
Motion Detection (Mtr)	10
Detection Angle	140°
PIR Sensitivity	No



Wattage	6.5
Beam Angle	90° x 90°
Energy Efficiency	Class G
Energy Usage	6.5KwH/1000H
Lumen output (lm)	500
Colour Temperature (K)	3700 - 4200
LED Type	SMD (Intergrated)
Mounting Hole Centres (mm)	60
Standby Consumption	<0.3W
ON Time Adjustment	5 Seconds to 10 Minutes
Lux Level	2 to 200, User Adjustable
Detection Range (Mtr)	10
Permanent ON Facility	No
Dusk Till Dawn	Yes
Multiple Unit Support	No
Cable Capacity (mm2)	2.5mm2
Cable Entry(s)	Back Entry

#### General

Weight (g)	323
Height (mm)	205
Width (mm)	108
Depth (mm)	78.5
Body Construction	Polycarbonate



## Data sheet **LED88PIRN**

Light / LED Bulkheads

Product Colour	Black
Accessories (Included)	Fittings
EAN Number	5012483015100
Guarantee Period	3 Years

### **Line Diagrams**



