



HANGING HOOK WITH MAGNETS



PORTABLE HAND-HELD SIZE



MULTI-POSITIONAL KICK STAND



**PS-IL10R - USB RECHARGEABLE INSPECTION LIGHT**  
NEW



1000  
LUMEN  
OUTPUT

3-32  
HOURS  
RUNTIME

64  
METRE  
BEAM RANGE

IP54  
DUST + WATER  
RESISTANCE

- 1000 Lumen White Samsung® SMD LEDs
- Additional 250 Lumen torch in the head
- Ultra strength aluminium and polycarbonate housing
- DC-USB charging cable (included)
- Red-to-Green charging indicator
- Integral hanging hook and strong magnet for hands-free use
- Multi positional hook / foldable kick stand
- IP54 dust and water resistant
- Impact resistant to 1m



MULTI-POSITIONAL KICK STAND



DC-USB CABLE (INCLUDED)

**BATTERY** 3.7v 5000 mAh Li-ion Rechargeable Battery (inc.)  
**WEIGHT** 338g (with battery)  
**DIMENSION** 205 x 60 x 42mm