

Comfortable chemical-resistant gloves, delivering highly durable personal protection

- **Elevated comfort:** AlphaTec® Solvex® 37-676 safety gloves' cotton flocking absorbs perspiration
- **Enhanced grip:** Their reversed lozenge finish grants them better grip, for secure handling
- **Specialized protection:** A high-performance nitrile compound composition delivers EN 374 Type A chemical resistance
- **Optimized durability:** AlphaTec® Solvex® 37-676 industrial gloves nitrile composition ensures longer wear time with ANSI/ISEA 105-2024 ABRASION LEVEL 5 and EN ABRASION LEVEL 4 resistance.
industrial gloves' with their EN level 4 and ANSI level 5 abrasion resistance
- **Guaranteed dexterity:** Their slightly thicker 17 mil/0.43mm make-up belies their ample dexterity
- **Food handling compliance:** Ideal in both wet and dry conditions, these AlphaTec® gloves comply with EU and FDA food handling regulations

Industries

- Automotive
- Food Processing
- Metal fabrication
- Oil and gas
- Chemical
- Agriculture
- Automotive Aftermarket
- Utilities
- Warehousing

Applications

- Delivery of parts to production line
- All food processing applications that have food contact
- Forging operations
- General pumping work
- Handling incoming goods
- Filling, blending and charging of raw materials
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Testing
- Opening furnaces draining pumps valves



AlphaTec® Solvex®

37-676

Excellent chemical protection with a good level of grip, fit and comfort

Previously known as: Solvex® 37-676

Key Features

- **Cotton flocking:** Moisture absorbency, for improved wearer comfort
- **Reversed lozenge finish:** Enhanced grip, for safer handling
- **Tough nitrile compound:** Heightened durability and chemical defenses

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate (ZDBC)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards

ANSI/ISEA 105-2024



EN388: 2016



4101X

EN ISO 374-1:2016 Type A



JKLOPT

EN ISO 374-5



VIRUS



G2
ISO 18889



G2
ISO 18889



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® Solvex® 37-676	Liner Material: N/A Coating Material: Nitrile	7, 8, 9, 10, 11	330 / 13	Green	• 12 pairs per bag, 12 bags per carton • Vend pack variant, 1 pair per polybag, 144 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell