






REVISIONS

			APVD.



*NEXT: A*

- 36/45-45db
- 36/12-43db
- 36/78-45db
- 45/12-53db
- 45/78-51db
- 12/78-62db



*NEXT: B*

- 36/45-46db
- 36/12-44.2db
- 36/78-43.2db
- 45/12-51db
- 45/78-48.8db
- 12/78-60.5db

Specification

Materials:

- Case: UL-94V-0 ABS WITH BLACK COLOR
- Jack: RJ-45 8P8C , 50 micro inches gold plated [ UL-94V-0 PBT]
- PCB:FR-4

STP : RJ-45/SHIELDED TO RJ-45/SHIELDED



UNLESS OTHERWISE SPECIFIED TOLERANCE : X. ±0.2 ANGLES : ±2° X.X ±0.1 X.XX ±0.05 DO NOT SCALE DRAWING		GRA		CAT5E INLINE COUPLER	
DRAWN BY <b>ANDY</b>	SIZE A	UNIT MM	PART NO. <b>E-IC-S-JJ-0</b>		
CHECKED BY <i>Andy</i>	SCALE 1 : 1	THIRD ANGLE PROJECTION 		PAGE 1 OF 1	
APPROVED BY <i>Andi</i>	DWG NO.		ITEM NO.		DATE 06/21/2001