



"x"	Switch function
B	on - (mom)
C	off - mom

Specifications:

Contact rating: 1A, 250V AC / 3A, 125V AC
 2A, 24V DC
Contact resistance: 30mOhm max.
Insulation resistance: 500MOhm min. at 500V DC
Dielectric strength: 1 000V, 50Hz for the duration of 1 minute
Operating temperature: -45°C to +110°C
Mechanical life: min. 30 000 cycles
Soldering conditions: hand-soldering: max.: 305°C, 3sec., 20W
Mounting: bushing M6x0.75
Button color: orange
Material: Contacts: coin silver
 Terminals: solder tags



Tolerances:			Date	Name	MSP 103 x	20 09 04	Page 1/1
			11/08	dr			
knitter-switch							
Modifications	Date	Name					