Features

- 2.50M Long
- H05VVF3G1.00
- Black Colour
- IEC C13 female PRC/3 Plug GB 2099 GB 1002

RS PRO 2.00m Power Cable C13 to PRC/3 10A-250 V

RS Stock No.: 0857444



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- RS Pro power cable assembly in black colour with length 2.50 meters. The product withstands current up to 10 Amps. This IEC cable assembly has a fully moulded Chinese PRC/3 GB 2099 GB 1002 plug on one end and fully moulded C13 IEC Connector on the other end.

General Specifications

Connector A	C13, IEC Straight female, EN /IEC 60320
Connector B	Chinese PRC/3 GB 2099 GB 1002 Straight male, IEC 60884
Power Cord Rating	10A- 250V
Sheath Colour	Black

Mechanical Specifications

Length	2.50m

Electrical Specifications

Power Cord Rating	10A- 250v
Visual Inspection	100%
Electrical Testing	100%
High pot test wire to wire	3.00Vac. for 2 sec.
Continuity Test	25Aac to grounding /20Aac to line and neutral
Polarity Test	Yes
Skin High Pot test	6:000 line to skin


Protection Category

Environmental Conformity	EU-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (R

Approvals

C13 Connector	CE, CCC
Chinese PRC/3 GB 2099 GB 1002	CCC
Cable	Harmonized <HAR>

2500 +/- 50



All dimensions in mm