



Cut



Cold



Medium Duty

Protecting workers from the elements.

- ActivArm[®] 97-011 Cold Weather Hi-Viz gloves are specially designed with an exclusive black double-dipped sandy nitrile coating that contrasts with a high-visibility orange liner in low-light and low-visibility conditions. And they protect the entire hand from the effects of wind, liquid and cold. This best-in-class combination does it all without compromising the dexterity and movement that is essential for getting the job done.
- Temperature and finger dexterity definitely affects performance and productivity for workers in extreme, cold environments. As temperatures drop, dexterity decreases. These conditions are compounded by the complexity of cold temperatures, which impair reflex time, dexterity, grip and feel. The visibility of ActivArm 97-011 Cold Weather Hi-Viz gloves, combined with superior protection from the elements and enhanced grip, mean a safer, more productive workforce.



Industries

- Chemical
- Construction

Applications

- Loading trucks & vehicles
- Product shipping, transport and delivery
- Cold Storage
- Construction
- Maintenance

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

97-011

Cold weather Hi-Viz gloves

Key Features

- 2-ply acrylic brushed liner keeps hands warm in extreme cold, as well as cut and abrasion protection
- Tested to perform at -4°F/-20°C
- ☑ double-dipped nitrile coating has a sandy finish for excellent wet/oily and dry materials handling, preventing injury from slippage
- Superior all-day comfort reduces hand fatigue
- More breathable than leather, keeping hands dry and comfortable
- Increases worker safety when high visibility is a must, including low-light conditions

Performance Standards & Regulatory Compliance



REACH Compliant

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm® 97-011	Dipped, Nitrile, Acrylic, Polyester, Knitwrist	10	8, 9, 10, 11	240-275 mm; 9.64-10.82	Black	• 6 pairs per box; 12 boxes in a carton



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region
Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia
Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro, Mexico
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2018 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

