

**NEMIQ**<sup>®</sup>  
The smart choice



AS SC-S-D-PIC TL44



## AS SC-S-D-PIC TL44

Assortment box 746 pcs., Terminal blocks and Push-in, Disconnect & Splicing



### Product Properties:

Nominal voltage	450 V
Nominal current	24-32 A
Transparent	Yes
Number of clamp positions	2-8 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Multi-coloured

### Dimensions:

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm <sup>2</sup>

Conductor cross section solid (solid, stranded)	0.2-4 mm <sup>2</sup>
MOQ	1 .
Unit	pcs
Nominal cross section	0.2-4 mm <sup>2</sup>
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
--------------------------	-----

### **Compliance:**

REACH	No SVHC (Latest. 05 Nov 2025)
-------	-------------------------------

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Assortment Boxes
Search Description	SORTIMENT, SKH2025MK
Alternative SKU	ASSC-S-D-PICTL44

### **Logistic information:**

Barcode	733117642701
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC-S-D-PIC TL44
Taric code	85369010
Unit	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.