



ENGLISH

## Datasheet

Stock No: 821-396

# RS Pro Stainless Steel Extension Spring



## Product Details

### Stainless Steel Extension Springs

Material to DIN 17224 No. 1 4310 or BS2056 EN58A with a right hand helix

All dimensions conform to DIN 2097 (Grade 2)

## Specifications:

Material	Stainless Steel
Free Length	27.2mm
Maximum Extended Length	95.70mm
Outside Diameter	4mm
Wire Diameter	0.36mm
Initial Tension	3.55N
Spring Rate	0.048N/mm