



# S/SC/SOV 102 Multipole Plugs

All dimensions see note 1)




Contact polarity A

Contact polarity Z




CONTACT CONFIGURATION	Contacts	Solder cup $\phi$		Crimp cup $\phi$ <sup>(2)</sup>
102 A Z 051	2	0.79		-
102 A Z 052	3	0.79		-
102 A Z 053	4	0.79		0.60
102 A Z 054	5	0.79		0.60
102 A Z 056	7	0.43		0.43
102 A Z 059	9	0.43		-

Keying codes (View from F)



Contact configuration for polarity A (View from B)

Contact configuration for polarity Z (View from B)



All dimensions in mm

Rev.

Pages

Notes :

- 1) All tolerances resulting from connector assembly are typically  $\pm 0.3mm$
- 2) For optimum crimping refer to available crimping manual.
- 3) Max cable diameter with unsealed clamp set. Max  $\phi 4.3mm$  with sealed clamp set.

Part number example : S 102 A056-130+

600471

1b

1/1



www.fischerconnectors.com