



TECHNICAL DETAILS 3000 – SERIES INDICATORLIGHTS

TYPE	3130	3135	3160	3161	3220	3221
Supply Voltage 120 – 440Vac NEONS EN 60598-1 approved	yes	yes	yes	yes	yes	yes
Max. Temperature Average Life (hours)	T120 25.000	T55 25.000	T120 25.000	T55 25.000	T120 25.000	T120 25.000
Possibility Splashproof Sealing	yes	no	yes	yes	yes	yes
Supply Voltage Up to 50 Volts AC/DC LEDS	Electrical approval not applicable					
Lens with diffusor	yes	no	yes	yes	yes	yes
Max. Temperature Average life (hours)	T50 >50.000	T50 >50.000	T50 >50.000	T50 >50.000	T50 >50.000	T50 >50.000
Possibility Splashproof Sealing	yes	no	yes	yes	yes	yes
Screwterminals with Locked up screws	all types NEON and LED indicator lights					