

210015

Link pipe cutter

for steel, SML and cast iron pipes

Code	ETIM
4536250	EC000148
EAN	UNSPSC
4017981210034	27-11-15-13
Country of origin	eClass
Germany	21-04-03-02
Customs tariff number	
82034000	



Article description

- Low space requirements due to ratchet-type operation
- In the standard version suitable for pipes from 85 to 175 mm Ø
- Expandable for tubes up to max. 330 mm outer-Ø
- Painted blue

Article information

Contents (Qty of pieces)	1	Wall thickness [min./max.]	3,2-8,0
Net weight [kg]	5,7 kg	Pipe diameter [max.] [mm]	175 mm
Pipe diameter [min.] [mm]	85 mm	Pipe diameter [min./max.] [inch]	-
Wall thickness [min.]	3,2 mm	Pipe diameter [min./max.] [mm]	85-175
Wall thickness [max.]	8,0 mm		