







Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Technical upright
Application	Multi-purpose
For enclosure nominal dimensions	1500 mm
Mounting support	Step slide Direct fixing on the rear inserts
Range compatibility	Thalassa PLA
Device composition	2 upright
Material	Steel

Complementary

Surface finish	Zinc coated
Fixing mode	Bosses inserts - screw type M8 - rear of enclosure location
Adjustment	Adjustable in depth every 25 mm with caged nuts Adjustable in height every 2.5 mm with quarter-turn nuts
Height	1500 Mm nominal: 1375 mm real:
Width	45 mm
Depth	34 mm
Thickness	2 mm
Cut-out dimensions	11 x 13 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------