


Monitor Arm, height-adjustable, 4 joints



The perfect viewing angle every time! The height-adjustable Monitor Arm with 4 joints ensures you can always effortlessly position your screen precisely where you want it. The height-adjustable Monitor Arms are ideal for users in different shapes and sizes and for staff who only need a screen on a temporary basis. The item Monitor Arms hold flatscreen monitors weighing between 2 and 10 kilograms in the desired position. The standard-compliant VESA connection (VESA 75 and 100) can be removed, fitted to the display and then clipped back into place on the Monitor Arm. There is also a practical pivot function for turning the screen through 90°. The arms feature clean cable routing and consistent compatibility with the Line 8 groove.



Scope of Delivery

1 monitor arm, 4 joints, die-cast Al
1 cable guide
1 Vesa adapter 75 and 100
1 profile adapter
Fastening elements

Technical note

The weight of the monitor is balanced by an adjustable gas pressure spring.

[0.0.678.76](#) Please click here for further information!

Properties	
Article number	0.0.678.76
Delivery unit	1 set
Weight	2.13 kg
Max. load-carrying capacity	2-10 kg

Accessoires	
0.0.633.99	Table Upright F 1500
0.0.634.02	Table Upright E 1500
0.0.670.55	Table Upright F 2 F Open, half-height
0.0.670.64	Table Upright E Open, half-height
0.0.671.49	Table Upright F 1500 Open
0.0.665.27	Table Upright F 2 F 1500 Open
0.0.722.03	Monitor Arm Keyboard Shelf
0.0.722.74	Laptop Holder