

Impact Driver LXT®

DTD152

18V • 1/4" • 165 Nm • 0 – 2 900 min⁻¹

Compact impact driver for quick driving

A compact and light impact driver with a 1/4" hex drive shank. A small and light tool that is easy to use but offers a max. fastening torque of 165 Nm, suitable for quick driving. A handy LED light for added lighting.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 2900 min ⁻¹
Max Fastening Torque Impact Drill	165 Nm
Impacts per Minute (IPM)	0 - 3500 min ⁻¹
Tightening Capacity Standard Bolt	M5 - M16
Driving Shank	1/4 "
Sound Power Level (L _{WA})	104 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	10,5 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- The screw tip is securely held in place by a quick lateral stroke
- Quick mount for 1/4 "screwdriver
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing