

M12 female contact Pack D0.8mm AWG 26-22



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9025
Specification	M12 female contact Pack D0.8mm AWG 26-22
HARTING eCatalogue	https://b2b.harting.com/21011009025

Identification

Category	Contacts
Series	Circular connectors M12
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm ²
Conductor cross-section	AWG 26 ... AWG 22

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances Lead

Commercial data

Packaging size	100
Net weight	0.17 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440204 Contact for industrial connectors