

FR50 - Bizflame Work FR Coverall

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre, 350g

Outer Carton: 10

Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM², ATPV 9.8 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM² (HAF=82%))

NO
IMAGE
AVAILABLE

Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement
- Concealed zip pocket
- Available in sizes from XS to 6XL
- Triple-stitched seams for extra durability
- 10 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays

FR50 - Bizflame Work FR Coverall

Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13136-03/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
FR50RETS	Red Tall	43.0	28.0	50.0	1.5700	0.0602	5036108362868	15036108851833
FR50RETM	Red Tall	43.0	28.0	50.0	1.6100	0.0602	5036108362851	15036108851826
FR50RETL	Red Tall	43.0	28.0	50.0	1.6720	0.0602	5036108362844	15036108851819
FR50RETXL	Red Tall	43.0	28.0	50.0	1.7080	0.0602	5036108362875	15036108851840
FR50RETXXL	Red Tall	43.0	28.0	55.0	1.7600	0.0662	5036108362882	15036108851857
FR50RETXXXL	Red Tall	43.0	28.0	55.0	1.7980	0.0662	5036108362899	15036108851864