



50567-959 T-shirt

Premium Performance - Modern fit

MASCOT® UNIQUE



60% cotton/40% polyester
195 g/m²



Single jersey fabric. Shrinkage max. 5%.

Industrial care category A1

Certifications



Logo

Logo placement:

- T-shirt logo. Mid-chest. Max 18x18 cm/7x7 inches
- T-shirt logo. Left breast. Max 12x10 cm/4.7x3.9 inches
- T-shirt logo. Vertical on left breast, read from the top downwards. Max 28x8 cm/11x3.1 inches
- T-shirt logo. Vertical on left breast, read from the bottom upwards. Max 28x8 cm/11x3.1 inches
- T-shirt logo. Right breast. Max 12x10 cm/4.7x3.9 inches
- T-shirt logo. Vertical on right breast, read from the top downwards. Max 28x8 cm/11x3.1 inches
- T-shirt logo. Vertical on right breast, read from the bottom upwards. Max 28x8 cm/11x3.1 inches
- T-shirt logo. On the back. Max 32x32 cm/12.5x12.5 inches
- T-shirt logo. Mid-nape. Max 12x5 cm/4.7x1.9 inches
- T-shirt logo. Under napeline. Max 12x5 cm/4.7x1.9 inches
- T-shirt logo. Special placement. Contact to discuss further



- Combed cotton absorbs moisture and is extra comfortable against the skin.
- Modern, close fit with great freedom of movement.
- Ribbed neck
- Neck yoke.
- Good space for placement of company logo.
- The product tolerates industrial washing.

Technical info

Two-toned. Combed cotton. Modern fit. Strong quality. Preshrunk Round neck Rib at neck Neckband.

User

