

QOU340

MINIATURE CIRCUIT BREAKER 240V 40A


[Download your QOU340 datasheet](#)

[Characteristics](#) | [Documents & Downloads](#)


Main

☐ Hide

Product or component type	Miniature circuit-breaker
Range of product	QOU
Circuit breaker type	Standard
[In] rated current	40 A
Poles description	3P
Short-circuit current	10 kA
Electrical connection	Slotted box lugs (line and load)
Circuit breaker application	HACR rated
Accessory / separate part type	None
Product certifications	CSA IEC UL listed
[Ue] rated operational voltage	240 V AC
Mounting mode	Unit mount
AWG gauge	AWG 14...AWG 2 (aluminium/copper)

Offer Sustainability

☐ Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  download Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

☐ Hide

Period	18 months
--------	-----------