



Miniature circuit-breaker

Part no.

PXL-C6/2

Article no.

236278



Powering Business Worldwide™

Technical data according to ETIM 4.0

Frequency		Hz	50 Hz
Voltage type			AC
Mounting depth		mm	69.5 mm
Rated current		A	6 A
Rated voltage		V	400 V
Trip type			C
Number of poles			2
Current-limiting class			3
Overvoltage category			3
Pollution degree			2
Width in space units			2
Protection type (IP)			IP20
Neutral conductor switching with pole			false
Rated switching capacity according to EN 60898		kA	10 kA
Rated switching capacity according to IEC 60947-2		kA	0 kA
Additional equipment possible			true