

Set of cable gland + nut stainless steel M12 AISI304L, IP68, UL approved

NSYCGX12

EAN Code: 3606481360212

Main

Range	PanelSeT	
Product or component type	Cable gland	
Accessory / separate part category	Cable management accessory	
Range compatibility	PanelSeT PanelSeT CRN PanelSeT PanelSeT S3D PanelSeT PanelSeT S3X	
Mounting location	Enclosure top Enclosure bottom	
Cable entry	Cable gland M12	
Device composition	1 cable gland 1 lock nut 1 seal	
Quantity per set	Set of 5	
Material	Body: stainless steel AISI 304L	

Complementary

Colour	Grey	
Fixing mode	Screwed By nut	
Height	28 mm	
Net weight	0.011 kg	

Environment

Product certifications	VDE
Flame retardance	V2 conforming to UL 94
Ambient air temperature for operation	-20100 °C permanent -40150 °C intermittent
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	2.000 cm
Package 1 Length	3.000 cm

Package 1 Weight	14.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Height	11.000 cm
Package 2 Width	28.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.796 kg
Unit Type of Package 3	P12
Number of Units in Package 3	2400
Package 3 Height	47.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	58.000 ka

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

○ Repack and remanufacture		
Take-back	No	