

27010200

Handheld Enclosure Taguan 130 80 / 70 x 125 x 36,7 /
28,5 mm**Zubehör** - s. Zeichnung
Accessories - see drawing

Handheld Enclosure Taguan 130 80 / 70 x 125 x 36,7 / 28,5 mm

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)

Technical data

Height	125 mm
Width	80 mm
Depth	36.7 mm
Material	ABS
Colour	ocean blue (RAL 5020)
Ingress protection	IP40
Degree of protection norm	EN 60529
temperature min.	-40 °C
temperature max.	80 °C
Surface resistance	4×10^{14} Ohm
Other versions on request	EMV

Commercial data

Country of origin	RO
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.13 kg
GTIN	4250157916655










ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

 27010090 Taguan Spare screw set	 27010280 Battery holder 4 micro-cells (AAA)
 27010281 Taguan 130 Monoblock holder	 27010282 Taguan 130 Clip
 27010285 Taguan Shaft cover RAL 5020	 27010287 Taguan Shaft cover infrared
 27010288 Taguan 130 Display screen set	 82100001 MEMBRANE KEYPADS FT 130b
 82100002 MEMBRAN KEYPADS FT 130e	