

Features

- Cat6A
- STP
- 50 x 25mm
- Euro Module

RS PRO Cat6A Clip in Euro Module

RS Stock No.: 0834518



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The CAT6A punch down module is 50 x 25mm punch down module to fit in faceplates.

General Specifications

Type	Jack
LAN Category	Cat6A
Shield Type	STP
Interface Type	RJ45
Length	50mm
Width	25mm
Depth	18.9mm

Mechanical Specifications

Housing Material	ABS
PCB Material	FR-4 Thickness 1.2mm
Contact material	Phosphor bronze stamp pin T=0.30mm
IDC Contact Material	Phosphor bronze T=0.5mm with tin plating
Wire	AWG 23-26

Electrical Specifications

Voltage Rating	125 VAC RMS
Current Rating	1.5 AMP
Contact Resistance	20 Milliohms Max
Insulation Resistance	100 Megohms Min @ 500 VDC
Dielectric Strength	750 VAC RMS 60Hz, 1Min

Approvals

Standards Met	CE UKCA REACH ROHS
---------------	--------------------

Similar Products

Stock No.	Brand	Product Name
0834602	RS PRO	Single Gang Euro Module Frame
0834590	RS PRO	Dual Gang Euro Module Frame
0834515	RS PRO	Cat6 Punch Down Euro Module
0834518	RS PRO	Cat6A Shielded Punch Down Euro Module

