

Robust cut-resistant work gloves, offering thermal and cut protection with added durability

- **Heightened protection:** ActivArm® 70-761 cut-resistant gloves meet ANSI/ISEA 105-2024 CUT A4 and EN ISO D standards. Their blend of DuPont™ Kevlar®, nylon, and acrylic also provides moderate abrasion resistance.
- **Enhanced features:** These industrial gloves also feature a reinforced thumb crotch made from 100% Kevlar®, for additional hand protection in this zone
- **Specialized defenses:** ActivArm® 70-761 protective gloves also satisfy EN 407 contact heat level 1 standards, for moderate thermal protection
- **Elevated comfort:** These safety gloves boast an ergonomic design shaped to natural hand contours, thereby protecting hands while offering wearers form-fitting comfort



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Chassis assembly, body trimming
- Welding
- Seizing rough blocs and cylinders
- Seizing and finishing structural parts
- Seizing structural parts
- Foundry operations
- Handling materials with sharp or rough edges
- Handling parts in high heat areas

Previously known as: Vantage® 70-761

Key Features

- **Exclusive fiber blend:** For durable, highly cut-resistant gloves
- **Reinforced aramid thumb crotch:** Reinforced personal protection
- **Thermal-protective design:** Moderate contact heat resistance

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 70-761	Liner Material: Aramid, Nylon, Acrylic Cuff Style: Knitwrist	10	6, 7, 8, 9, 10, 11	225-275 mm/ 8.85-10.82 inches	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.