



Product data sheet

Power tools for trade & industry

Cordless Telescopic Hedgecutter

PRO GHE 18V-50 TP

High-performance cordless hedgepole for trimming at height



The most important data

Battery voltage	18.0 V
Blade length	50 cm
Cutting speed	1,700 rpm

Part Number 0 600 8D5 000

Technical data

Technical data

Battery voltage	18.0 V
Blade length	50 cm
Battery recommendation	>=4.0Ah
Cutting speed	1,700 rpm
Stroke rate at no load nominal	3,400 spm
Weight excl. battery	4.5 kg
Packaging dimensions (width x length x height)	195 x 1192 x 190 mm



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cuts tall hedges easily thanks to 2.5 m telescopic pole
- Powerful performance with Brushless motor and variable speed control
- Cuts thicker branches without jamming thanks to the patented Bosch Anti-Blocking System

**HEAVY
DUTY**



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

